



HSIC10500FR, Heavy Wall Cross-Linked Black Polyolefin Heat Shrinkable End Cap, 1/0-500 kcmil Code, #1-313 kcmil Flex, 600 V, Fire Retardant.



By Burndy
Catalog # [HSIC10500FR](#)

Heavy Wall Cross-Linked Black Polyolefin Heat Shrinkable End Cap, 1/0-500 kcmil Code, #1-313 kcmil Flex, 600 V, Fire Retardant.

Features

- Heavy Wall Cross Linked Polyolefin
- UV94-V0
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermo-chromic lines disappear during correct installation
- Rated up to 600 Volts
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

Application

For Used To Insulating Exposed Conductors In Energized Applications

General

Catalog Number	HSIC10500FR
Color	Black
Connector Type	HEAVY WALL END CAP
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HSIC-FR, Heavy Wall, Fire Retardant
UPC	781810266557

Conductor Related

Conductor Range	ConductorRange
Conductor Size	1/0AWG - 500kvmil

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSIC10-500FR_LineArt](#)
- [Sales Drawings - SC209680-01](#)
- [Specifications - HSIC10500FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)