



# HSIC81FREA, Heavy wall heat shrinkable end cap, 0.50" ID Min. (Exp.), 0.16" ID Max.(Rec.), #8 - #4, Thick Wall, Black

By Burndy  
Catalog # [HSIC81FREA](#)

Heavy wall heat shrinkable end cap, 0.50" ID Min.(Exp.), 0.16" ID Max.(Rec.), #8 - #4, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.

## Features

- Heavy Wall Cross Linked Polyolefin
- UV94-VO
- Recognized Flame Retardant Material
- 3:1 Shrink Ratio
- Shrink Temperature of 150°C
- Blue Thermochromic lines disappear during correct installation
- Rated up to 600 Volts
- Sealing Adhesive
- Moisture and Water Resistant
- UL486D
- Insulates and Protects
- Direct Burial

## General

Catalog Number	HSIC81FREA
Color	Black
Material	POLYOLEFIN
UPC	781810083130

## Conductor Related

Conductor Range #4 AWG to #2/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	24000

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Product Cross Section Image\(s\) - BUR\\_HSIC-FR\\_LineArt](#)  
[Sales Drawings - SC209680-01](#)  
[Specifications - HSIC81FREA](#)  
[Video - Heat Shrink Product Overview & Installation](#)

