



HSTPBK06254FPK5EA, Thin Wall Polyolefin Heat Shrink Tubing, Black, 5-Pack, 4' Lengths, 5/8" ID

By Burndy

Catalog # [HSTPBK06254FPK5EA](#)

5/8 I.D., Qty 5 = 5 Pieces, Color = Black, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp., Store At 21°C.

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General



Catalog Number

HSTPBK06254FPK5EA

Color

Black

UPC

621945699915

Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin](#)

[Heat Shrink Expires 12-31-2024](#)

[Sales Drawings - 50139507](#)

[Specifications - HSTPBK06254FPK5EA](#)



A Hubbell brand