



HSTPBL004750FRL, Thin Wall Polyolefin Heat Shrink Tubing, Blue, 50' Reel, 3/64" ID

By Burndy
Catalog # [HSTPBL004750FRL](#)

3/64 I.D., 1 Unit = 50 Ft., Color = Blue, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General

Color	Blue
UPC	621945690004

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2023](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Sales Drawings - 50139507](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSTPBL004750FRL-SPEC-EN | REV 5/2024