



HSTPBL062525FRL, Thin Wall Polyolefin Heat Shrink Tubing, Blue, 25' Reel, 5/8" ID

By Burndy
Catalog # [HSTPBL062525FRL](#)



5/8 I.D., 1 Unit = 25 Ft., Color = Blue, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General

Catalog Number	HSTPBL062525FRL
Color	Blue
UPC	621945695238

Logistics

Carton Quantity	8
-----------------	---

Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Sales Drawings - 50139507](#)
[Specifications - HSTPBL062525FRL](#)