



HSTPCL1000100FRL, Thin Wall Polyolefin Heat Shrink Tubing, Clear, 100' Reel, 1" ID

By Burndy
Catalog # [HSTPCL1000100FRL](#)



1 I.D., 1 Unit = 100 Ft., Color = Clear, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General

Catalog Number	HSTPCL1000100FRL
Color	Clear
Material	Cross-linked Polyolefin
UPC	621945696198

Logistics

Carton Quantity 1

Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Sales Drawings - 50139507](#)
[Specifications - HSTPCL1000100FRL](#)