



## HSTPGR200025FRL, Thin Wall Polyolefin Heat Shrink Tubing, Green, 25' Reel, 2" ID

By Burndy

Catalog # [HSTPGR200025FRL](#)



2 I.D., 1 Unit = 25 Ft., Color = Green, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### General

Catalog Number                      HSTPGR200025FRL  
Color                                      Green

UPC    621945697355

### Logistics

Carton Quantity                              4

### Product Assets

- [Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Specifications - HSTPGR200025FRL](#)