



# HSTPWH037550FRL, Thin Wall Polyolefin Heat Shrink Tubing, White, 50' Reel, 3/8" ID

By Burndy  
Catalog # [HSTPWH037550FRL](#)



3/8 I.D., 1 Unit = 50 Ft., Color = White, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## General

Color	White
UPC	621945694415

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2023](#)



A proud member of the Hubbell Family.