



## HSTPWH062550FRL, Thin Wall Polyolefin Heat Shrink Tubing, White, 50' Reel, 5/8" ID

By Burndy

Catalog # [HSTPWH062550FRL](#)



5/8 I.D., 1 Unit = 50 Ft., Color = White, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### General

Catalog Number                      HSTPWH062550FRL  
Color                                      White

UPC    621945695528

### Logistics

Carton Quantity                              4

### Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Specifications - HSTPWH062550FRL](#)



A Hubbell brand