



# HSTPYL0125250FRL, Thin Wall Polyolefin Heat Shrink Tubing, Yellow, 250' Reel, 1/8" ID

By Burndy  
Catalog # [HSTPYL0125250FRL](#)



1/8 I.D., 1 Unit = 250 Ft., Color = Yellow, 2:1 Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## General

Color	Yellow
UPC	621945692473

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets

[Brochures - Polyolefin Thin Wall Heat Shrink Brochure](#)  
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2023](#)



A proud member of the Hubbell Family.