




Two Conductor Two Hole Mounting Stacked Aluminum Panel Board Set Screw Connector

By Burndy
Catalog # K11A34U2



Aluminum Universal Terminal, 2 Hole, Two: 4/0 AWG (Str)-500 kcmil, 1/4" Stud, .69" Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

Application

For Aluminum and Copper Conductors

General

Connector Type	Stacked
EU RoHS Indicator	Yes
Hex Key	3/8
Installation Torque Recommended in-lb	375 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370278
UPC 12 Digit	7818103702788

Dimensions

Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	2.31 in
Dimension - Height fraction	2.4 in
Dimension - Height inch	2.40 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	1.45 in
Dimension - Screw Size inch	15/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Dimension - Width fraction	1-11/25 in
Dimension - Width inch	1.44 in
Dimension - Width mm	37 mm

Electrical Ratings

Conductor Related

Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size Range	4/0 AWG-500 kcmil
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor Size	4/0 AWG-500 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - se210997](#)

Rating - Minimum Voltage 600



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-K11A34U2-SPEC-EN | REV 1/2024