



K3A2U2, AL Universal Terminal, 3 Conductor, #14-2 AWG Str, 2-Hole, 5/16" Stud, .88" Spacing, 3 Screws, Al/Cu Rated

By Burndy
Catalog # [K3A2U2](#)



Aluminum Universal Terminal, 3 Conductor, 2 Hole, 14-2 AWG (Str), 5/16" Stud, .88" Stud Hole Spacing, 3 Screws, Al/Cu Rated, Tin Plated.

Features

- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Application

For Aluminum and Copper Conductors

General

Catalog Number	K3A2U2
Connector Type	Parallel Set-Screw
EU RoHS Indicator	Yes
Installation Torque	50 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type Plated	Slot Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370360
UPC 12 Digit	7818103703600

Dimensions

Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	1.63 in
Dimension - Height fraction	5/8 in
Dimension - Height inch	0.62 in
Dimension - Hole Size fraction	11/32
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	55.62 mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.34 in
Dimension - Pad Width inch	1.64 in
Dimension - Stud Size inch	5/16 in
Dimension - Width fraction	1-59/100 in
Dimension - Width inch	1.64 in
Dimension - Width mm	40 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	14-2 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	14-2 AWG
Conductor Size	14-2 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size
Number of Conductors	3

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	216
Minimum Pack Quantity	1

Product Assets

[3D Models - K3A2U2_MODEL-IGES](#)
[3D Models - K3A2U2_MODEL-STEP](#)
[3D Models - K3A2U2_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_K3AU_LineArt](#)
[Sales Drawings - se210997](#)
[Specifications - K3A2U2](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-K3A2U2-SPEC-EN | REV 8/2024