

K21A36U2N, AL Universal Terminal, 2-Hole, 1/2" Holes, 1-3/4" NEMA Spacing

By Burndy
Catalog # [K21A36U2N](#)

Aluminum Universal Terminal, 2 Hole, 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing), tin plated.

Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

General

Catalog Number	K21A36U2N
Connector Type	Stacked
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810538616
UPC 12 Digit	7818105386166

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Height mm	0 mm
Dimension - Hole Size mm	0 mm
Dimension - L Length Overall mm	0 mm



Dimension - Thread Size	-
Dimension - Width mm	0 mm
Dimensions	5.34 in x 2.47 in x 3.00 in
Height	3 in
Length	5.34 in
Width	2.47 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	65
-----------------------	----

Product Assets

- [3D Models - K21A36U2N_MODEL-STEP](#)
- [3D Models - K21A36U2N_MODEL-PDF](#)
- [3D Models - K21A36U2N_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094861](#)
- [Specifications - K21A36U2N](#)