



K21A39U2N, 3 Conductor Panel Board, NEMA Spacing, Range: 1/0 AWG-750 kcmil, AL9CU, 1/2" Stud

By Burndy
Catalog # [K21A39U2N](#)

3 Cond. Panel Board with NEMA Spacing, Wire Range = 1/0 AWG - 750 kcmil; Dual Rated AL9CU; 1/2" Diameter Stud.

Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

General

Catalog Number	K21A39U2N
Connector Type	Stacked
Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	621945510180

Dimensions

Dimension - Bolt Size fraction 1/2



Dimensions	5.34 in x 2.75 in x 3.00 in
Height	3 in
Length	5.34 in
Width	2.75 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094862](#)
- [Specifications - K21A39U2N](#)