

KA44, Terminal, Use on for Copper Cable.

By Burndy
Catalog # KA44



Terminal, Use on for Copper Cable.

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

Application

Capable of joining wide range of cables to equipment pad or terminal block

General

Catalog Number	KA44
Connector Type	Terminal
EU RoHS Indicator	Yes
Hardware Type	1 1/8 UNF Hex SetScrew
Material	Copper
Material - Hardware	Stainless Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810252031

Dimensions

Dimension - B Length fraction	1-13/25 in
Dimension - B Length inch	1.52 in
Dimension - D inch	2.36 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Height mm	50.8 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm

Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.88 in
Dimension - N inch	0.67 in
Dimension - Pad Width inch	1.75 in

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	250 kcmil-800 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KA44](#)