

KA4CG15, #14 Solid - #4 Stranded Copper; #10 Stud; 45 in-lb recommended torque



By Burndy
Catalog # [KA4CG15](#)

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

General

Catalog Number	KA4CG15
Connector Type	Terminal
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	KA-LUG™
Type	Bolted Lugs & Terminals
UPC	781810146354
UPC 12 Digit	7818101463544

Dimensions

Dimension - Height fraction	11/20 in
Dimension - Height inch	0.55 in
Dimension - Height mm	14 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KA4CG15](#)