

KA34TN, Universal Terminal, #4 - 500 kcmil; 1/2" Stud; 375 in-lb recommended torque

By Burndy
Catalog # [KA34TN](#)



Universal Terminal, #4 - 500 kcmil; 1/2" Stud; 375 in-lb recommended torque.

General

Catalog Number	KA34TN
Connector Type	Terminal
Hardware Type	13/16 UNF Socket/HexScrew
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin - Electro Plated
Type	Bolted Lugs & Terminals
UPC	781810095195

Dimensions

Dimension - B Length fraction	1-3/25 in
Dimension - B Length inch	1.12 in
Dimension - Height fraction	2-8/89 in
Dimension - Height inch	2.09 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.38 in
Dimension - Stud Size inch	1/2

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC..074265-01](#)
[Specifications - KA34TN](#)