



KA4CTN, #14 Solid - #4 Stranded Copper; 1/4" Stud; 45 in-lb recommended torque; Tin plated

By Burndy
Catalog # [KA4CTN](#)



#14 Solid - #4 Stranded Copper; 1/4" Stud; 45 in-lb recommended torque; Tin plated.

General

Connector Type	Terminal
Hardware Type	5/16 UNF Slotted SetScrew
Installation Torque	45
Recommended in-lb	
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin - Electro Plated
Type	Bolted Lugs & Terminals
UPC	781810244463

Dimensions

Dimension - B Length inch	0.47 in
Dimension - Height inch	0.77 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in
Dimension - Stud Size inch	1/4

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc088846-01](#)



A proud member of the Hubbell Family.