

## KA44, Terminal, Use on for Copper Cable.

By Burndy  
Catalog # KA44



Terminal, Use on for Copper Cable.

### Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

### Application

Capable of joining wide range of cables to equipment pad or terminal block

### General

Catalog Number	KA44
Connector Type	Terminal
EU RoHS Indicator	Yes
Hardware Type	1 1/8 UNF Hex SetScrew
Material	Copper
Material - Hardware	Stainless Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810252031

### Dimensions

Dimension - B Length fraction	1-13/25 in
Dimension - B Length inch	1.52 in
Dimension - D inch	2.36 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Height mm	50.8 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm

Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.88 in
Dimension - N inch	0.67 in
Dimension - Pad Width inch	1.75 in

### Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	250 kcmil-800 kcmil
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	4
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - KA44](#)