

KA8CTN, #14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb recommended torque; Tin plated



By Burndy
Catalog # KA8CTN

#14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb recommended torque; Tin plated.

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks
- Tin plated

General

Catalog Number	KA8CTN
Connector Type	Terminal
Hardware Type	#12 UNC Slotted SetScrew
Material	Copper
Material - Hardware	Steel
Physical Attribute - Screw Type	Flat head round tip
Plated	Y
Plating Type	Tin Plated
Type	Bolted Lugs & Terminals
UPC	781810103913

Dimensions

Dimension - Height inch	15.42 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	20.6 mm
Dimension - Length Overall inch	0.81 in
Dimension - Mounting Hardware Bolt Size inch	12.24 UNC
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Width inch	0.38 in

Dimension - Width mm 9.70 mm

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	# 14 Sol. - # 8 Str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sc088846-01](#)
[Specifications - KA8CTN](#)