

KA4CG16, CU Terminal, #14 Solid - #4 Stranded Copper; 5/16 Stud

By Burndy
Catalog # KA4CG16



CU Terminal, #14 Solid - #4 Stranded Copper; 5/16 Stud.

Features

Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

General

Catalog Number	KA4CG16
Connector Type	Terminal
Hardware Type	5/16 UNF Slotted SetScrew
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Type	Bolted Lugs & Terminals
UPC	781810006269

Dimensions

Dimension - B Length fraction	8/17 in
Dimension - B Length inch	0.47 in
Dimension - Height fraction	67/87 in
Dimension - Height inch	0.77 in
Dimension - Hole Size inch	0.32 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in

Conductor Related

Conductor - Copper Solid Size Range	14;13;12;11;10;9;8;7;6;5;4
Conductor - Copper Solid Size	14-4
Conductor - Copper Str Size Range	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Size	14-4
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	59400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sc088846-01](#)
[Specifications - KA4CG16](#)