



KAP750, 750 kcmil pin adaptor, Torque: 450 N lb, Voltage: 600 V.

By Burndy
Catalog # [KAP750](#)

750 kcmil pin adaptor, Torque: 450 N lb, Voltage: 600 V.



Features

-
-
-
-
-
-

Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

General

Connector Type	Center Formed Adapter
EU RoHS Indicator	Contact Manufacturer
Hex Key	1/2 in
Installation Torque Recommended in-lb	500
Material	Aluminum
Sub Brand	Pin Adaptor
Type	350 - 750 Mechanical Pin Adaptor; Centered Pin
UPC	621945493346

Dimensions

Dimension - Strip Length inch	2.30 in
Dimensions	4.46 in x 1.87 in x 2.37 in
Height	2.37 in
Length	4.46 in
Outside Diameter	1.75 in
Width	1.87 in

Electrical Ratings

Amperage Rating	535 A
-----------------	-------

Conductor Related

Conductor - AL Str Size Range	350 kcmil - 750 kcmil
Conductor - Copper DLO Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex H Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex I Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex K Size Range	350 kcmil - 750 kcmil
Conductor - Copper Str Size Range	350 kcmil - 750 kcmil
Conductor Size	350-750 KCMIL

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50076514](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KAP750-SPEC-EN | REV 5/2024