



# KA8C, Copper Terminal, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud, 1 Screw.

By Burndy  
Catalog # [KA8C](#)



Copper Terminal, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud, 1 Screw.

## Features

Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

## Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

## General

Connector Type	Terminal
EU RoHS Indicator	Yes
Hardware Type	#12
Material	Copper
Material - Hardware	Steel
Physical Attribute - Screw Type	Flat head round tip
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810362051

## Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Height inch	15.42 in
Dimension - Hole Size fraction	7/32
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	20.6 mm
Dimension - Length Overall inch	0.81 in
Dimension - Mounting Hardware Bolt Size inch	12.24 UNC
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Width inch	0.38 in
Dimension - Width mm	9.70 mm

## Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	# 14 Sol. - # 8 Str.
Conductor Size	14-8 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - KA8C\\_MODEL-IGES](#)
- [3D Models - KA8C\\_MODEL-STEP](#)
- [3D Models - KA8C\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_KA\\_Lineart](#)
- [Sales Drawings - sc088846-01](#)



A proud member of the Hubbell Family.

