

KAPO350R, Wire range: 1/0 -350 kcmil, Torque: 450 N lb.

By Burndy
Catalog # KAPO350R



Wire range: 1/0 -350 kcmil, Torque: 450 N lb.

Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

General

Catalog Number	KAPO350R
Connector Type	Offset
Material	Aluminum
Type	<ul style="list-style-type: none"> • 1/0 -350 kcmil Mechanical Pin Adaptor • Off-Centered Pin
UPC	621945554160

Dimensions

Dimensions	2.75 in x 1.56 in x 2.06 in
Height	2.06 in
Length	2.75 in
Outside Diameter	1.38
Width	1.56 in

Electrical Ratings

Amperage Rating	350
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size Range	1/0 AWG - 350 kcmil
Conductor - Copper DLO Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex H Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex I Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex K Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Str Run	1/0 -350 kcmil
Conductor - Copper Str Size Range	1/0 AWG - 350 kcmil
Conductor Size	1/0 AWG- 350 KCMIL

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KAPO350R](#)