



KLU175, Copper Terminal, Offset Tongue, 1 Hole, 4-3/0 AWG (Str), 3/8" Stud, 1 Screw

By Burndy
Catalog # [KLU175](#)



Copper Terminal, Offset Tongue, 1 Hole, 4-3/0 AWG (Str), 3/8" Stud, 1 Screw.

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

General

Catalog Number	KLU175
Connector Type	Pressure Bar
EU RoHS Indicator	Yes
Hardware Type	3/8 UNF Socket/HexScrew
Installation Torque	120
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351406

Dimensions

Dimension - B Length fraction	22/31 in
Dimension - B Length inch	0.71 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.20 in
Dimension - N inch	0.43 in
Dimension - Pad Width inch	0.75 in
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	4 AWG-3/0 AWG
Conductor Size	4-3/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KLU_LineArt](#)
[Sales Drawings - sd207469-01](#)
[Specifications - KLU175](#)



A Hubbell brand