



KAPO750, 750 kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.

By Burndy
Catalog # [KAPO750](#)

750 kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.



Features

-
-
-
-
-
-

Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

General

Connector Type	Offset
EU RoHS Indicator	Contact Manufacturer
Hex Key	1/2 in
Installation Torque	500
Recommended in-lb	
Material	Aluminum
Sub Brand	Pin Adaptor
Type	350 - 750 Mechanical Pin Adaptor; Off-Centered Pin
UPC	621945493377

Dimensions

Dimension - Strip Length inch	2.30 in
Dimensions	4.46 in x 1.87 in x 2.37 in
Height	2.37 in
Length	4.46 in
Outside Diameter	1.75 in
Width	1.87 in

Electrical Ratings

Amperage Rating	535 A
-----------------	-------

Conductor Related

Conductor - AL Str Size Range	350 kcmil - 750 kcmil
Conductor - Copper DLO Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex H Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex I Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex K Size Range	350 kcmil - 750 kcmil
Conductor - Copper Str Size Range	350 kcmil - 750 kcmil
Conductor Size	350-750 KCMIL

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50076514](#)



A proud member of the Hubbell Family.