



**KLU175H, Cu SCRULUG Terminal W/
Hex Head Bolt, #4 - 3/0 Str. Cu,
3/8" Stud Hole**

By Burndy
Catalog # [KLU175H](#)

Cu SCRULUG Terminal W/ Hex Head Bolt, #4 - 3/0 Str. Cu, 3/8"
Stud Hole.



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

General

Catalog Number	KLU175H
Connector Type	Terminal
Hardware Type	3/8 UNF Socket/HexScrew
Installation Torque	124 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810463413
UPC 12 Digit	7818104634133

Dimensions

Dimension - B Length fraction	22/31 in
Dimension - B Length inch	0.71 in
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.20 in
Dimension - N inch	0.43 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	4 AWG-3/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KLU175H](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KLU175H-SPEC-EN | REV 8/2024