

KK3A40U2N, AL Universal Terminal, 3 Conductor, 300-800 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, 6 Screws, Al/Cu Rated

By Burndy
Catalog # [KK3A40U2N](#)



Aluminum Universal Terminal, 3 Conductor, 2 Hole, 300-800 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 6 Screws, Al/Cu Rated, Tin Plated.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

General

| | |
|--------------------------------------|-------------------------|
| Catalog Number | KK3A40U2N |
| Connector Type | Parallel Set-Screw |
| EU RoHS Indicator | Yes |
| Material | Aluminum |
| Material - Hardware | Aluminum |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin Plated |
| Sub Brand | UNIVERSAL TERMINAL |
| Type | Bolted Lugs & Terminals |
| UPC | 781810600474 |

Dimensions

| | |
|--|----------|
| Dimension - Bolt Hole Size inch | 0.56 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - Height inch | 1.89 in |
| Dimension - Height mm | 48 mm |
| Dimension - Hole Size fraction | 9/16 |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Hole Size mm | 14 mm |
| Dimension - L Length Overall mm | 157 mm |
| Dimension - Length Overall inch | 6.19 in |
| Dimension - N inch | 0.63 in |
| Dimension - Pad Width inch | 4.28 in |
| Dimension - Stud Size inch | 0.56 in |

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - AL Str Size | 300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil |
| Conductor - AL Str Size Range | 300-800 Kcmil |
| Conductor - Copper Str Size Range | 300-800 Kcmil |
| Conductor Size | 300-800 KCMIL |
| Conductor Type | <ul style="list-style-type: none"> CU C Str-Size AL C Str-Size |
| Number Of Wires | 3 |

Certifications And Compliance

| | |
|---|--|
| Buy American Compliant | Contact Manufacturer |
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Certified Listed | BABA Compliant (All status valid till December 2024) |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 12 |

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_KK3A-U_LineArt](#)
[Sales Drawings - se210997](#)
[Specifications - KK3A40U2N](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-KK3A40U2N-SPEC-EN | REV 1/2025