

# KKA36U2N, AI Universal Terminal, 2 Holes, #2 AWG (STR)-600 KCMIL, 1/2 IN Stud, 1.75 IN Spacing, 5.50 IN L, Tin Plated

By Burndy  
Catalog # [KKA36U2N](#)



AI Universal Terminal, 2 Holes, #2 AWG (STR)-600 KCMIL, 1/2 IN Stud, 1.75 IN Spacing, 5.50 IN L, Tin Plated.

## Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

## General

Catalog Number	KKA36U2N
Connector Type	Terminal
Installation Torque	550
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Type	Bolted Lugs & Terminals
UPC	781810124437

## Dimensions

Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.25 in
Dimension - Height fraction	1-17/32 in
Dimension - Height inch	1.52 in
Dimension - Height mm	38.6 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.39 in
Dimension - Stud Size inch	1/2

## Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 AWG-600 kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	2 AWG-600 kcmil
Conductor Size	2 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics


Minimum Pack Quantity	1
Pallet Quantity	36

## Product Assets

[3D Models - KKA36U2N\\_MODEL-IGES](#)  
[3D Models - KKA36U2N\\_MODEL-STEP](#)

[3D Models - KKA36U2N\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - se210997](#)  
[Specifications - KKA36U2N](#)



©2024 Hubbell Incorporated. All rights reserved  
BRDY-KKA36U2N-SPEC-EN | REV 10/2024