

KPA4CTPG3, Copper Lug, #14 Sol-4 Str, 1/4" Stud

By Burndy
Catalog # [KPA4CTPG3](#)



Mechanical Connector; 14 Sol.-4Str.; 1/4 " stud.

Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

General

Catalog Number	KPA4CTPG3
Connector Type	Terminal
Installation Torque	45 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810079867

Dimensions

Dimension - D inch	0.71 in
Dimension - Height fraction	1 in
Dimension - Height inch	1.00 in
Dimension - Height mm	25.4 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7.1 mm

Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.28 in
Dimension - N inch	0.33 in
Dimension - Pad Width inch	0.50 in

Conductor Related

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd207546-01](#)
- [Specifications - KPA4CTPG3](#)