



KS15, Split Bolt Connector, Run/Tap: #10-8 AWG Str

By Burndy
Catalog # [KS15](#)



Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap).

Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Catalog Number	KS15
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	80 in-lbs
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011256
UPC 12 Digit	7818100112566

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	0.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	14 AWG-8 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor - CopperWeld	#8

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486UL467CSA C22.2 No 41
Standards - Industry Standards Met	<ul style="list-style-type: none">UL486UL467CSA C22.2 No 41
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	99000

Product Assets

- [3D Models - KS15_MODEL-STEP](#)
- [3D Models - KS15_MODEL-IGES](#)
- [3D Models - KS15_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section E2 - Mechanical Grounding](#)
- [Catalogs - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)

Conductor - CopperWeld
Solid Tap #8
Conductor - CopperWeld Str
Run #8
Conductor - CopperWeld Str
Run Range #8
Conductor Type

- CU C Solid-Run
- CU C Str-Run
- CU Weld C Solid-Run
- CU Weld C Str-Run
- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap
- CU C Solid-Tap



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KS15-SPEC-EN | REV 6/2024