



KS23, Split Bolt Connector, Run/Tap: #6 AWG-#2 AWG Str

By Burndy
Catalog # [KS23](#)

Copper Split Bolt, Cu: 6 AWG-2 AWG (Str) (Run & Tap).



Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Catalog Number	KS23
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	275
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810012758
UPC 12 Digit	7818100127588

Dimensions

Dimension - B Length fraction	18/25 in
Dimension - B Length inch	.72 in
Dimension - Cross Flats inch	0.82 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.54
Dimension - Width fraction	31/50 in
Dimension - Width inch	0.62 in
Dimension - Width mm	16 mm
Width	0.62 in

Conductor Related

Conductor - Copper Solid Run	1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	1 AWG
Conductor - Copper Solid Tap Range	14 AWG-1 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Run Range	6 STR - 2 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 STR - 2 STR
Conductor - CopperWeld Solid Run	#1
Conductor - CopperWeld Solid Run Range	#1
Conductor - CopperWeld Solid Tap	#1
Conductor - CopperWeld Solid Tap Range	#1
Conductor - CopperWeld Str Run	3 #7;3A;5D
Conductor - CopperWeld Str Run Range	3 #7-5D
Conductor - CopperWeld Str Tap	3 #7;3A;5D
Conductor - CopperWeld Str Tap Range	3 #7-5D
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct	Yes

Burial	
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry	RUS
Standards Met	
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	44000

Product Assets

- [3D Models - KS23_MODEL-PDF](#)
- [3D Models - KS23_MODEL-IGES](#)
- [3D Models - KS23_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section E2 - Mechanical Grounding](#)
- [Catalogs - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
- [Sales Drawings - SD.078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KS23-SPEC-EN | REV 6/2024