

KVS44, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS44](#)



Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURUM bolts in place during installation. Installed with ordinary wrench, wrench size: 15/16 cross flats.

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper And Copperweld, Heavy Duty Connections

General

Catalog Number	KVS44
EU RoHS Indicator	Yes
Installation Torque	500 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS
UPC	781810064603
UPC 12 Digit	7818100646033

Dimensions

Dimension - Height inch	3.71 in
Dimension - Height mm	94.24 mm
Dimension - Stud Size inch	5/8 in
Dimension - Width inch	3.03 in

Conductor Related

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor - Copper Str Tap Range	3/0 str.- 1000 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run • CU Weld C Solid-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards	UL486C
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KVS_Lineart](#)
- [Sales Drawings - SC..052062-01](#)
- [Specifications - KVS44](#)