



KVSW26, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW26](#)

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 2 str. - 2/0 str., Tap:6 sol. - 2/0 str.



General

Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810065457
UPC 12 Digit	7818100654577

Dimensions

Dimension - Height inch	1.76 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/16 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 str. - 2/0 str.
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	6 sol. - 2/0 str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - KVSW26_MODEL-STEP](#)
[3D Models - KVSW26_MODEL-IGES](#)
[3D Models - KVSW26_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_KVSW_LineArt](#)
[Sales Drawings - sd009323-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KVSW26-SPEC-EN | REV 5/2024