



# HYTOOL™ Hand-Operated Crimper, BG (5/8) and D3 grooves; 24" Straight fiberglass handles

By Burndy  
Catalog # MD64



Crimper, BG & D3 Grooves; 24" Straight Fiberglass Handles.

## Application

Crimping

## General

|                          |   |
|--------------------------|---|
| Application - For Use On | Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors |
| Catalog Number           | MD64  |
| Crimp Force Capacity     | 4.5 ton   |
| Die Type                 | W Die and X Die   |
| EU RoHS Indicator        | Yes   |
| Tool Type                | Hand Operated Crimper   |
| Trade Name               | HYTOOL™   |
| Type                     | Crimper   |
| UPC                      | 781810446058  |
| UPC 12 Digit             | 7818104460588   |

## Dimensions

|        |         |
|--------|---------|
| Length | 31.5 in |
| Weight | 8.25 lb |
| Width  | 7.5 in  |

## Conductor Related

Crimping Ranges

Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

## Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Buy American Compliant             | Yes |
| Standards - RoHS Compliance Status | EX  |

## Logistics

|                       |           |
|-----------------------|-----------|
| Minimum Pack Quantity | 1         |
| Package Contents      | Tool only |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MD68\\_LA](#)
- [Sales Drawings - sd208984-01](#)
- [Specifications - MD64](#)