



Full Cycle Ratchet Crimper, #10-4 AWG HYLUG™.

By Burndy
Catalog # [MR4CQ](#)



Full Cycle Ratchet Crimper, #10-4 AWG HYLUG™.

Features

- Reinforced heavy duty back with high strength aluminum body
- Fully protected ratchet mechanism does not allow handles to open until full cycle is completed
- Inspection gauges available to check each groove (sold separately)
- Spring loaded indenter jaw, keeps jaws closed

Application

Crimping

General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR4CQ
Die Type	Permanent Die Grooves
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810772058
UPC 12 Digit	7818107720588

Dimensions

Height	1 in
Length	11.75 in

Conductor Related

Crimping Ranges	#10 - #4 AWG
-----------------	--------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MR4C_LineArt](#)
- [Sales Drawings - 39171](#)
- [Specifications - MR4CQ](#)