



Full Cycle Ratchet Crimper for Nuclear Applications, #22 AWG-10 AWG

By Burndy
Catalog # [MR10G6](#)



Full Cycle Ratchet Crimper, Nuclear, #22-10 AWG.

Features

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

Application

Crimping

General

Application - For Use On	Nylon Insulated Terminals
Catalog Number	MR10G6
Die Type	Permanent Die Grooves
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810029961
UPC 12 Digit	7818100299611

Dimensions

Length 11.15 in

Conductor Related

Crimping Ranges #22 - #10 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MR10G6_LineArt](#)
[Sales Drawings - 30004893](#)
[Specifications - MR10G6](#)