



# Full Cycle Ratchet Crimper, #12-6 AWG INSULUG™

By Burndy  
Catalog # [MR410M](#)



Full Cycle Ratchet Crimper, #12-6 AWG INSULUG™.

## Features

- Heat treated steel working parts

## Application

Crimping

## General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR410M
Die Type	Permanent Die Grooves
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810772065
UPC 12 Digit	7818107720655

## Dimensions

Dimensions	11.75 in x 8.91 in x 1.00 in
Height	1 in

Length	11.75 in
Width	8.91 in

## Conductor Related

Crimping Ranges	#12 - #6 AWG
-----------------	--------------

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MR410M\\_LineArt](#)
- [Sales Drawings - sd028976-01](#)
- [Specifications - MR410M](#)