



Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Aluminum

By Burndy
Catalog # [MRC840AL](#)

Crimper, #8-4/0 AWG AL.

Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

Application

Crimping

General

Application - For Use On	Aluminum Terminals and Splices
Catalog Number	MRC840AL
Die Type	Rotating Die Wheel
Tool Type	Mechanical Rotating Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810492840
UPC 12 Digit	7818104928400

Dimensions

Dimensions	26.00 in x 8.00 in x 1.50 in
Height	1.5 in



Length	26 in
Width	8 in

Conductor Related

Crimping Ranges	Aluminum: #8 AWG - #4/0 AWG
-----------------	-----------------------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - BUR_10103462_MRC840AL](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MRC840_lineart](#)
- [Sales Drawings - 10105533](#)
- [Specifications - MRC840AL](#)