

N2AH3444N, Substation - Copper Terminal

By Burndy
Catalog # N2AH3444N

Substation Connectors.



Application

Substation

General

Catalog Number	N2AH3444N
Connector Type	Terminal
Installation Torque	480
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Pad Configuration	4 x 4 - 4 holes
Physical Attribute - Pad Orientation	Offset
Plated	N
Plating Type	Unplated
UPC	781810117729
UPC 12 Digit	7818101177299

Dimensions

Dimension - B Length inch	2.63 in
Dimension - D inch	4.00 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	178 mm
Dimension - Length Overall inch	7.00 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	5.38 in
Dimension - Width mm	137 mm
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	1/0 -500 kcmil
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa207485-01](#)