



# Full Cycle Ratchet Crimper, #9-4 AWG Uninsulated (bare) Terminals and Splices.

By Burndy  
Catalog # [MR4C](#)



Full Cycle Ratchet Crimper, #9-4 AWG Bare.

## Features

- Full cycle ratchet mechanism
- Spring loaded indenter holds connector
- Long handles
- Reinforced heavy duty aluminum back

## Application

Crimping

## General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR4C
Die Type	Permanent Die Grooves
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810772003
UPC 12 Digit	7818107720033

## Dimensions

Dimensions	11.75 in x 3.62 in x 1.00 in
Height	1 in

Length	11.75 in
Weight	2.3 lb
Width	3.62 in

## Conductor Related

Crimping Ranges	#9 - #4 AWG
-----------------	-------------

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_082\\_OUIF\\_MR4C\\_lineart](#)
- [Sales Drawings - 28819](#)
- [Specifications - MR4C](#)