



N2AH4444N, Substation - Copper Terminal

By Burndy
Catalog # N2AH4444N

Substation Connectors.



Application

Substation

General

Catalog Number	N2AH4444N
Connector Type	Terminal
Installation Torque	480
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Pad Configuration	4 x 4 - 4 holes
Physical Attribute - Pad Orientation	Offset
Plated	N
Plating Type	Unplated
UPC	781810053577
UPC 12 Digit	7818100535777

Dimensions

Dimension - B Length inch	2.88 in
Dimension - D inch	4.00 in
Dimension - Height inch	2.25 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	186 mm
Dimension - Length Overall inch	7.32 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	6.12 in
Dimension - Width mm	155 mm
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	4/0 AWG-1000 kcmil
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - N2AH4444N_MODEL-PDF](#)
- [3D Models - N2AH4444N_MODEL-IGES](#)
- [3D Models - N2AH4444N_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa207485-01](#)



A Hubbell brand