

# NA14A2N90, Substation - Aluminum Bolted Terminal

By Burndy  
Catalog # [NA14A2N90](#)

Substation Connectors.



## Application

Substation

## General

Catalog Number	NA14A2N90
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.62 x 3 - 2 holes
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
UPC	781810166383
UPC 12 Digit	7818101663833

## Dimensions

Dimension - B Length inch	3.25 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	1.41 in
Dimension - Height inch	3.28 in
Dimension - Height mm	83.3 mm
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.03 in

Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.62 in
Dimension - Width inch	2.80 in
Dimension - Width mm	71 mm

## Conductor Related

Conductor - AL Tube Std Size	3/4 IPS
Conductor - AL Tube Std Size Range	3/4 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	3/4 IPS
Conductor - Copper Tube Std Size Range	3/4 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• AL Tube Std-Size</li> <li>• CU Tube Std-Size</li> </ul>
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50004695](#)  
[Specifications - NA14A2N90](#)