

NA152N90, Substation - Copper Terminal

By Burndy
Catalog # NA152N90

Substation Connectors.



Application

Substation

General

Catalog Number	NA152N90
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.88 x 3 - 2 holes
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
UPC	781810030769
UPC 12 Digit	7818100307699

Dimensions

Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	2.56 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.21 in
Dimension - N inch	0.62 in

Dimension - Pad Width inch	1.88 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	11
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD021664-01](#)
- [Specifications - NA152N90](#)