

## NA15A4NCG2, Substation - Aluminum Bolted Terminal

By Burndy  
Catalog # [NA15A4NCG2](#)

Substation Connectors.



### Application

Substation

### General

Catalog Number	NA15A4NCG2
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	621945137875
UPC 12 Digit	6219451378755

### Dimensions

Dimension - B Length inch	3.50 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	1.50 in
Dimension - Height inch	3.38 in
Dimension - Height mm	85.9 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - N inch	0.63 in

Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.06 in
Dimension - Width mm	78 mm

### Conductor Related

Conductor - AL Tube Std Size	1 IPS
Conductor - AL Tube Std Size Range	1 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	<ul style="list-style-type: none"> <li>AL Tube Std-Size</li> <li>CU Tube Std-Size</li> </ul>
Number of Conductors	1

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50019250](#)  
[Specifications - NA15A4NCG2](#)