

NA122N, Substation - Copper Terminal

By Burndy
Catalog # [NA122N](#)

Substation Connectors.



Application

Substation

General

Catalog Number	NA122N
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	2 holes
Plated	N
Plating Type	Unplated
UPC	781810065990
UPC 12 Digit	7818100659900

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.50 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - Pad Width inch	1.50 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	3/8 IPS
Conductor - Copper Tube EH Size Range	3/8 IPS
Conductor - Copper Tube Std Size	3/8 IPS
Conductor - Copper Tube Std Size Range	3/8 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	18
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa006759-01](#)
- [Specifications - NA122N](#)