


NA172N, Substation - Copper Terminal, 1-1/2" IPS, 2-Hole NEMA

By Burndy
Catalog # NA172N

Cast Copper Alloy Bolted Terminal, Cu Tube To Flat, 1-1/2" IPS, 2-NEMA Pad Holes, .56" Hole Dia.



Application

Substation

General

Catalog Number	NA172N
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	2.5 x 3 - 2 holes
Plated	N
Plating Type	Unplated
UPC	781810002469
UPC 12 Digit	7818100024699

Dimensions

Dimension - B Length inch	2.69 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-3/4
Dimension - Height inch	2.75 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	151 mm
Dimension - Length Overall inch	5.94 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.50 in
Dimension - Width inch	3.94 in
Dimension - Width mm	100 mm

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	1 1/4 IPS
Conductor - Copper Tube EH Size Range	1 1/4 IPS
Conductor - Copper Tube Std Size	1 1/4 IPS
Conductor - Copper Tube Std Size Range	1 1/4 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_NA132N_LineArt](#)
[Sales Drawings - sa006759-01](#)
[Specifications - NA172N](#)