

# Substation - Aluminum Bolted Terminal

By Burndy  
Catalog # [NA17A34N](#)



Substation Connectors.

## Application

Substation

## General

Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810145814
UPC 12 Digit	7818101458144

## Dimensions

Dimension - B Length inch	4.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	1.76 in
Dimension - Height inch	3.88 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.64 in
Dimension - Width mm	92 mm

## Conductor Related

Conductor - AL Tube Std Size	1 1/2 IPS
Conductor - AL Tube Std Size Range	1 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> <li>• AL Tube Std-Size</li> <li>• CU Tube Std-Size</li> </ul>
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA038849-01](#)

