

Substation - Copper Terminal

By Burndy
Catalog # [NA152N](#)

Cast Copper Alloy Bolted Terminal, Cu Tube To Flat, 1" IPS, 2-NEMA Pad Holes, .56" Hole Dia.



Application

Substation

General

Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.88 x 3 - 2 holes
Plated	N
Plating Type	Unplated
UPC	781810002339
UPC 12 Digit	7818100023399

Dimensions

Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-1/8
Dimension - Height inch	2.06 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.25 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.88 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	1 IPS
Conductor - Copper Tube EH Size Range	1 IPS
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[3D Models - NA152N_MODEL-IGES](#)
[3D Models - NA152N_MODEL-STEP](#)
[3D Models - NA152N_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sa006759-01](#)

