

NA17A4NTMH149, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # NA17A4NTMH149

Substation Connectors.



Application

Substation

General

Catalog Number	NA17A4NTMH149
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810119082
UPC 12 Digit	7818101190822

Dimensions

Dimension - B Length inch	4.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.88 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in
Dimension - N inch	0.63 in

Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.64 in
Dimension - Width mm	92 mm

Conductor Related

Conductor - AL Tube Std Size	1 1/2 IPS
Conductor - AL Tube Std Size Range	1 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	1 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> AL Tube Std-Size CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sa038849](#)
[Specifications - NA17A4NTMH149](#)